

Plug & Play Analytical Solutions

Making Basic Measurements Easy



A Complete Solution Package

Exceeding Expectations for Routine Measurements

The easy Line is designed around one central requirement: ease-of-use. From system selection to commissioning, operation and maintenance, all system components are narrowly tailored to eliminate all unnecessary hassle. The result: an unique solution in terms of convenience and performance for measuring pH, ORP, dissolved oxygen and conductivity.

When no-fuss measurement solutions are required, choices abound but results can be vary widely. From component selection to configuration through cumbersome calibration, time can be lost before tangible results are obtained. But with the METTLER TOLEDO easy Line, Plug & Play components fit together easily for maximum compatibility and simplicity of use.

An unique concept

The easy Line relies on digital technology for seamless communication between the transmitter and the sensors. This includes serial number, factory and user calibration, for Plug and Play measurement convenience. Simply connect the easy-SenseTM sensors and the M200 easy does the rest. The same multiparameter transmitter can be used for all sensor types: pH, ORP, oxygen and conductivity.

Flexible multi-parameter solutions

Water pre-treatment management is simple using the easy Line for pH adjustment or dechlorination monitoring with ORP measurement. Dual easySense conductivity sensors monitor RO membrane performance with on-line percent rejection computation. At the other end of the plant, wastewater treatment is controlled effectively using easySense dissolved oxygen and pH sensors.

Savings in all phases

The M200 easy models offer panel, wall or pipe mounting with one or two channels of measurement for any combination of parameters. This greatly simplifies specification, documentation, purchasing, installation, startup, maintenance and spare parts. The cost of ownership is minimized at every project step.

Package for system fabricators

The easy Line particularly addresses the requirements of applications, where turn-key solutions are important:

- make-up water & pre-treatment
 - applications: chemical injection control, purity monitoring, pH adjustment
- primary filtration
 - applications: filter effectiveness, purity monitoring
- reverse osmosis and desalination
- % rejection for membrane performance, pH pre-treatment



System fabricators



Utilities




Water pre-treatment

As Easy as 1-2-3

Getting Started has Never Been so Easy

With system elements that are fully compatible, time-consuming component selection is a thing of the past. The result: the measurement loop is up and running in no time.



M200 easy Multi-Parameter Transmitters

All-in-one Solution With Maximum Convenience

One transmitter, four measurement parameters: the versatile M200 easy minimizes your costs of ownership. Thanks to pre-calibrated digital sensors, minimal transmitter configuration is needed.

M200 easy $\frac{1}{2}$ DIN



M200 easy 1/4 DIN

When expectations for a field device go beyond just good measurement, the M200 easy is convincing with its exceptional user-friendliness. It accepts all digital easySense sensors without the need for calibration or configuration.

For commissioning, a user-friendly "Quick Setup" routine will guide you through the first settings.

Your benefits

Faster commissioning

Factory calibrated sensors can be installed and replaced without the need for recalibration at the measurement point.

Error-free configuration

Pre-calibrated sensors carrying their own data save installation time.

Large, easy-to-read interface

Intuitive operation for higher convenience and productivity gain.

Selected specifications of the M200 easy

M200 easy pH, ORP, dissolved oxygen, conductivity Parameters Channels single or dual Power 100 to 240 V AC, or 20 to 30 V DC, 10 VA Enclosure Relays 2-SPDT mechanical rated at 250 V AC, 3 Amps resistive Digital input 2 (1 for single channel) User interface 4-line backlit LCD, 5-button key pad Password protection two or four 0/4 to 20 mA, 22 mA alarm, galvanically isolated from Current outputs input and from earth/ground Service interface USB Analog sensors pH, ORP, dissolved oxygen, conductivity Digital easySense sensors M200 easy 1/4 DIN Order number M200 easy 1/2 DIN 52 121 555 52 121 554 Single channel: Dual channel: 52 121 557 52 121 556

easySense™ Conductivity Sensors

For Wide Application Coverage

The proven easySense™ sensors are designed for trustworthy performance with the convenience of digital technology. Their wide measurement range allows for installation in many applications.

With the easySense™ conductivity sensors, no need to key in the cell constant in the transmitter: the "Plug & Play" digital technology transmits all sensor data to the transmitter in seconds and without errors.

The 2-electrode sensors are ideal for measurement at low to very low conductivity, in filtration, pre-treatment or Reverse Osmosis (RO) applications. The 4-electrode sensor covers medium-conductivity wastewater applications.

Because the high performance measuring circuits are located right in the sensor bodies, measure-

Your benefits

Complete application coverageCompact choice of rugged and versatile sensors.

Time-saving installation

Plug & Play sensors carry their own calibration cell constant.

Low cost of ownership

Long-lasting sensors that do not require heavy maintenance.

ments are unaffected by cable resistance, capacitance or electrical noise susceptibility. Electrical connections are simplified and the digital signal is unaffected by cable length.

easySense Conductivity 71



easySense Conductivity 72



easySense Conductivity 73



easySense Conductivity 77



Selected specifications of easySense™ Conductivity sensors

	71	72	73	77		
Туре	2-electrode	2-electrode	2-electrode	4-electrode		
Cell constant	0.1 cm ⁻¹	0.1 cm ⁻¹	0.1 cm ⁻¹	0.350 cm ⁻¹		
Measuring range	0.12000 µS/cm	0.12000 µS/cm	0.12000 µS/cm	0.02400 mS/cm		
System accuracy	±3.0 % or better	±3.0 % or better	±3.0 % or better	±5.0 % or better		
Temperature compensation	standard high purity, cation, ammonia, Light 84, isopropanol, glycol					
Temperature sensor	30 kOhm NTC	30 kOhm NTC	30 kOhm NTC	30 kOhm NTC		
Wetted parts	Titanium	Titanium	Titanium	1.4435 SS (316L)		
Insertion fitting	3/ ₄ " NPT	⅓" NPT	3/4" NPT & subm.	3/ ₄ " NPT		
Cable Length/Order nr						
- 7.6 m (25 ft)	58 031 300	58 031 302	58 031 304	_		
- 30.5 m (100 ft)	58 031 301	58 031 303	58 031 305	=		
 K8S connector 	_	_	_	52 003 810		

easySense™ pH/ORP & Oxygen Sensors

Top Performance Meets Convenience

When your basic applications require a reliable and longlasting measurement point, easySense™ sensors are the answer. Using proven technology, they withstand harsh process conditions and are easy to use.

pH measurement often requires skilled personnel in order to maintain and calibrate the sensors. easySenseTM sensors are pre-calibrated, with no specialist knowhow required for sensor replacement at the measurement point.

Designed using METTLER TOLEDO's long-standing expertise in process analytics, the easySense pH sensors are problem-solvers for basic applications. The easySense O₂ 21 sensor for dissolved oxygen (DO) uses rugged membranes that can easily be replaced in minutes.

Your benefits

Long sensor lifetime

Leads to lower replacement costs – even under harsh process conditions.

Reliable design

METTLER TOLEDO technology for use in basic applications.

No need for pH buffers at startup

Pre-calibrated sensors do not require a first on-site calibration.

easySense pH 31



easySense pH 32, 33, 34



easySense ORP 41



easySense O₂ 21



Selected specifications of easySense™ pH/ORP and oxygen sensors

	31	32	33	34	41	21
Parameter	pН	рН	рН	pН	ORP	Oxygen
Measurement range	014	014	014	014	n. a.	0.03 ppm –
						100% satu-
						ration
Temperature	−5…80°C	−5…80°C	−580°C	−5…80°C	−5…80°C	060°C
	23176°F	23176°F	23176°F	23176°F	23176°F	32140°F
Pressure resistance	02 bar	0.52 bar				
	029 psig	729 psig				
Pressure resistance	06 bar	_	_	=	06 bar	=
040°C/32104°F	087 psig				087 psig	
Reference system	Argenthal	Argenthal	Argenthal	Argenthal	Argenthal	_
	(Ag/AgCI)	(Ag/AgCI)	(Ag/AgCI)	(Ag/AgCI)	(Ag/AgCI)	
Reference electrolyte	gel	pressurized gel	pressurized gel	pressurized gel	polymer	_
Diaphragm	1 ceramic	1 ceramic	1 ceramic	1 ceramic	open junction	
Membrane glass	HA	HA	HF	LoT	Platinum ring	_
Application	general purpose	harsh processes	HF resistant	low temperature	general purpose	general purp.
Plug head	K8S, Pg 13.5	K8S, Pg 13.5				
Order number	52 003 771	52 003 768	52 003 770	52 003 769	52 003 772	52 206 406

easy Housings

Your Quickest Connection to the Process

Housings represent the physical link between your process and the measurement system, providing a secure connection without complicated installation steps. The easy Line housings do just that.

Housings must provide a correct placement of the sensor in the process, as well as withstand the sometimes harsh temperature, pressure and chemical conditions imposed by the process.

easy Housings are designed for the typical conditions that prevail in light industrial and utilities applications.

Their reliable and proven design make them a preferred choice for long-lasting operation and fast installation.

Your benefits

Wide selection of installationsSolutions for installation in vessels, pipes and open basins.

Versatility

A choice of high-quality materials for medium to harsh process conditions.

Variable immersion length

Selectable immersion length for easy installation in each application.

easyFit 21, 22



easyFlow 21, 22



easyFlow 23



easyDip 21, 22



Selected specifications of easy housings

	easyFit 21	easyFit 22	easyFlow 21, 22	easyFlow 23	easyDip 21, 22
Material	CPVC	1.4404	CPVC	Polysulfon	PVC
Temperature	-585°C	−10100°C	-580°C	−10130°C	080°C
	23185°F	14212°F	23176°F	14266°F	32176°F
Max pressure	06.8 bar	03.4 bar	03.4 bar	06.8 bar	ambient
	0100 psig	050 psig	050 psig	0100 psig	
Max temperature	65°C/149°F	85°C/185°F	85°C/185°F	85°C/185°F	
Order number	52 403 951	52 403 952	easyFlow 21:	52 403 955	easyDip 21:
- US size			52 403 953		52 403 956
			easyFlow 22:		easyDip 22:
- metric size			52 403 954		52 403 957

Get On-line Support

via www.mt.com/pro

Visit our website at any time for fast and competent information. The very latest, updated product and support documentation is available in many different languages.

Support center with easy and free download

- Declaration of conformity
- Certificates
- Description of equipment
- User manuals/data sheets



Visit our website for fast and competent information.

For on-line access click on

- Contact us
- Request more information
- Get a quote

■ Country-specific information

 Select country/area to get access to your local support

Search functionality

Enter keyword to find requested information

Find and download product and application documents

- Product News
- Industry Newsletters
- Application News

www.mt.com/pro

Visit for more information

Sales and service:





Management System certified according to ISO 9001 / ISO 14001

Mettler-Toledo AG

Process Analytics Im Hackacker 15, CH-8902 Urdorf Phone +41 44 729 62 11 Fax +41 44 729 66 36

Subject to technical changes.
© 08/2009 Mettler-Toledo AG.
Printed in Switzerland. 52 121 503